

SatPax® HA-R

Pre-wetted Sealed Edge Cleanroom Laundered 100% Polyester Knit Wiper

SatPax® HAR is a ultrasonically sealed edge cleanroom laundered wiper composed of 100% continuous filament polyester knit fabric pre-wetted with Isopropyl alcohol. This pre-wetted format provides a cost-effective and easy-to-use solution versus traditional bulk handling of solvents, maintenance of squirt bottles and inconsistent wetting and cleaning associated with wetting a dry wiper during cleaning. A high solution saturation level of 65% makes SatPax® HAR Ideal for regulated applications or applications requiring higher solution levels delivered to the surface.



Key Attributes

- 100% continuous filament polyester knit
- Ultrasonically sealed edge for reduced fibre contamination
- Laundered and packaged in Berkshire's ISO Class 4 cleanroom
- Pre-wetted with a consistent 70% IPA/ 30% DI Water concentration and 60% saturation level
- Re-sealable solvent resistant packaging

Benefits

- Critically low particles, fibres, ions and extractables
- High abrasion resistance
- Reduces alcohol usage and preparation / handling costs
- Reduces VOC emissions
- Increases cleaning efficiency
- Increases cleaning protocol consistency

Environmental

- Registered under REACH

Other Class 3 and above Pre-wetted wipers

- SatPax® 3000
- SatPax® ValuSeal® 1500
- SatPax® MicroSeal® 1200

Applications

- Designed for use in ISO Class 3 and higher cleanroom environments
- Designed for use in wet cleaning of critical surfaces where control of flammable solvents and flammable solvent concentrations is required
- Final cleaning of surfaces or products prior to manufacturing or packaging

Alcohol Mixtures

Alcohol / DI Water mixtures can be varied to fit the customer requirements. Typical mixtures are 70/30 and 9/91 IPA/DI Water.

Saturation Levels

The amount of solution contained in each wiper can be varied according to customer requirements. Higher saturation levels apply more solution to the surface during cleaning.

Sterile Validated Option

For aseptic processing areas, the same wiper material can be provided in a gamma irradiated validated sterile to a 10⁻⁶ sterility assurance level.

www.berkshire.uk.com

Contact: Tel + 44 1953 562800
 enquiries@berkshire.uk.com

| | | |
|---------|----------------------|----------------------------|
| America | Tel 1 413 528 2602 | info@berkshire.com |
| Europe | Tel + 44 1953 562800 | enquiries@berkshire.uk.com |
| SE Asia | Tel 65 6252 4313 | enquiries@berkshire.com.sg |
| Japan | Tel 81 3 4530 9883 | master@berkshire.co.jp |

Technical Data (In Dry State)

| Attribute | | Units | Value | Test Method |
|-----------------------------|------------------|-----------------------------------|---------------|---|
| Basis Weight | | g/m ² | 136 | TAPPI T-410 |
| Caliper | | µm | 435 | TAPPI T-411 |
| Fibres | ≥100µm | fibres/cm ² | 0.080 | IEST-RP-CC004.4 Sec 7.1.3 /Sec 7.2.2 modified |
| Particles | ≥0.5µm | x10 ³ /cm ² | 0.31 | IEST-RP-CC004.4 Sec 7.1.3 /Sec 7.2.1 modified |
| Sorbency | Capacity | mL/m ² | 567 | IEST-RP-CC004.4 Sec 9.1 /Sec 9.2 modified |
| | Efficiency | mL/g | 4.2 | |
| | Rate | seconds | 1 | |
| Non-Volatile Residue | DI Water | g/m ² | 0.0042 | IEST-RP-CC004.4 Sec 8.1.2 |
| | IPA | g/m ² | 0.0092 | |
| Ions | Na ⁺ | ppm | 0.41 | IEST-RP-CC004.4 Sec 8.2.2 |
| | K ⁺ | ppm | 0.048 | |
| | Ca ⁺⁺ | ppm | 0.035 | |
| | Mg ⁺⁺ | ppm | 0.0085 | |
| | Cl ⁻ | ppm | 0.21 | |

Notes:

- Technical data represented in this table are typical values at the time of publication. These should not be used as product specifications.
- Due to differences in test methods applied and equipment utilised by different wiper manufacturers, valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions
- Third party testing can be performed upon request

Order Information:

| Product | Number | Size | Shts/pk | Pks/cs | IPA/DI | Saturation | VOC % by Weight | Style |
|--------------|---------------|----------------|---------|--------|--------|------------|-----------------|--------|
| SatPax® HA-R | SPXHAR.001.12 | 9x9" (23x23cm) | 30 | 12 | 70/30 | 60% | 42% | J-fold |

For more information on our other contamination control products or technical consultation, please contact your Berkshire Sales Representative or e-mail: info@berkshire.uk.com

Other Berkshire products



Wipers



Glove Liners



Mop Systems



Documentation Systems



Face Masks



Swabs